



PATRIOT® 129 Series Latch Head Battery Cutter, No Batteries, No Charger, Hard Case

By Burndy
Catalog # PATCUT129LILCB

PATCUT129 Latch Head Battery Cutter, No Batteries or Charger, Hard Case.

Features

- Special latch head design provides interference free closure for mid-span cuts
- 180° Head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold

Application

Cutting

General

Application - For Use On	ACSR, Aluminum, Copper Cable; Ground Rod; Rebar; Soft Steel Bolts; Standard Guy; EHS Guy Strand
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PATCUT129LILCB
Container Type	Hard Case
Crimp Force Capacity	7 ton
Power Source	No Charger
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutter
UPC	781810540909
UPC 12 Digit	7818105409099

Dimensions

Dimensions	14.50 in x 3.50 in x 13.50 in
Height	13.5 in
Length	14.5 in
Weight	9.85 lb
Width	3.5 in

Conductor Related

Crimping Ranges	Cutting Capacity: Copper/Aluminum up to 1.29"; ACSR up to 1113 kcmil; Ground Rod up to 5/8"; Rebar up to 1/2"; Soft Steel Bolts up to 5/8"; Standard Guy up to 1/2"; EHS Guy Strand up to 3/8"
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Cutter, Lanyard, Hard Case

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Specifications - PATCUT129LILCB](#)