



# PATRIOT® 129 Series Latch Head Battery Cutter, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Nylon Pro Bag

By Burndy  
Catalog # PATCUT129LIPB



PATCUT129 Latch Head Battery Cutter, 3Ah Li-ion, AC, Nylon Pro Bag.

## Features

- Special latch head design provides interference free closure for mid-span cuts
- 180° Head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold

## Application

Cutting

## General

Application - For Use On	ACSR, Aluminum, Copper Cable; Ground Rod; Rebar; Soft Steel Bolts; Standard Guy; EHS Guy Strand
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PATCUT129LIPB
Container Type	Nylon Pro Bag
Crimp Force Capacity	7 ton
EU RoHS Indicator	Yes
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutter
UPC	621945561977
UPC 12 Digit	621945561977

## Dimensions

Dimensions	14.50 in x 3.50 in x 13.50 in
Height	13.5 in
Length	14.5 in
Weight	9.85 lb

Width 3.5 in

## Electrical Ratings

Operating Voltage 18 VDC

## Conductor Related

Crimping Ranges Cutting Capacity:  
Copper/Aluminum up to 1.29";  
ACSR up to 1113 kcmil; Ground  
Rod up to 5/8"; Rebar up to  
1/2"; Soft Steel Bolts up to 5/8";  
Standard Guy up to 1/2"; EHS  
Guy Strand up to 3/8"

## Certifications And Compliance

Buy American Compliant No  
Standards - RoHS Compliance EX  
Status

## Logistics

Carton Quantity 1  
Minimum Pack Quantity 1  
Package Contents Cutter, (2) Batteries, Charger,  
Lanyard, Nylon Pro Bag  
Pallet Quantity 12

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50106125](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)  
[Specifications - PATCUT129LIPB](#)

