



PATRIOT® 1500 Series Battery Cutter for Copper and Aluminum, (1) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Nylon Pro Bag

By Burndy
Catalog # [PATCUT1500L5PB](#)



PATCUT1500 Battery Cutter for CU/AL, 5Ah Li-ion, AC, Nylon Pro Bag.

Features

- Variable speed trigger
- Forward/Reverse switch features a locking position
- Large, strategically placed, non-skid bumper
- LED Worklight
- Accepts 2.0Ah-6.0Ah Makita batteries

Application

Cutting

General

Application - For Use On	Aluminum, Copper Cable
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PATCUT1500L5PB
Container Type	Nylon Pro Bag
Power Source	120V-AC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutter
UPC	621945562400
UPC 12 Digit	621945562400

Dimensions

Dimensions	6.00 in x 4.38 in x 15.50 in
Height	15.5 in
Length	6 in
Weight	6.9 lb
Width	4.38 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Cutting Capacity: Aluminum up to 1500 kcmil, Copper (Soft Drawn) up to 1000 kcmil (Do Not Cut Steel or ACSR)
-----------------	--

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Cutter, (1) Battery, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50106125](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PATCUT1500L5PB](#)
[Video - PATCUT1500 Series Cutter](#)
[Video - BURNDY Pro Bag, BURNDY Minute](#)