



# PATRIOT® 1500 Series Battery Cutter for Copper and Aluminum, No Battery, No Charger, Hard Case

By Burndy  
Catalog # PATCUT1500LCB

PATCUT1500 Battery Cutter for CU/AL, No Battery or Charger, Hard Case.



## Features

- Variable speed trigger
- Forward/Reverse switch features a locking position
- Large, strategically placed, non-skid bumper
- LED Worklight
- Accepts 2.0Ah-6.0Ah Makita batteries

## Application

Cutting

## General

Application - For Use On	Aluminum, Copper Cable
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Hard Case
EU RoHS Indicator	No
Power Source	No Charger
Sub Brand	Cable cutter
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutter
UPC	621945541184
UPC 12 Digit	621945541184

## Dimensions

Dimensions	6.00 in x 4.38 in x 15.50 in
Height	15.50 in
Length	6.00 in
Weight	6.90 lb
Width	4.38 in

## Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

## Conductor Related

Crimping Ranges	Cutting Capacity: Aluminum up to 1500 kcmil, Copper (Soft Drawn) up to 1000 kcmil (Do Not Cut Steel or ACSR)
-----------------	--

## Logistics

Minimum Pack Quantity	1
Package Contents	Cutter, Lanyard, Hard Case

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50093502](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-PATCUT1500LCB-SPEC-EN | REV 1/2024