



PATRIOT® 1500 Series Battery Cutter for Copper and Aluminum, No Battery, No Charger, Nylon Pro Bag

By Burndy
Catalog # PATCUT1500LCBPB



PATCUT1500 Battery Cutter for CU/AL, No Battery or Charger, Nylon Pro Bag.

Features

- Variable speed trigger
- Forward/Reverse switch features a locking position
- Large, strategically placed, non-skid bumper
- LED Worklight
- Accepts 2.0Ah-6.0Ah Makita batteries

Application

Cutting

General

Application - For Use On	Aluminum, Copper Cable
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PATCUT1500LCBPB
Container Type	Nylon Pro Bag
EU RoHS Indicator	No
Power Source	No Charger
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutter
UPC	621945562417
UPC 12 Digit	621945562417

Dimensions

Dimensions	6.00 in x 4.38 in x 15.50 in
Height	15.5 in
Length	6 in
Weight	6.9 lb
Width	4.38 in

Electrical Ratings

Operating Voltage 18 VDC

Conductor Related

Crimping Ranges Cutting Capacity: Aluminum up to 1500 kcmil, Copper (Soft Drawn) up to 1000 kcmil (Do Not Cut Steel or ACSR)

Certifications And Compliance

Buy American Compliant No
UL Listed No

Logistics

Carton Quantity 1
Minimum Pack Quantity 1
Package Contents Cutter, Lanyard, Nylon Pro Bag
Pallet Quantity 12

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50106124](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PATCUT1500LCBPB](#)