



PATRIOT® IN-LINE® 6-Ton Scissor Action, 430 Dieless Crimper Jaw for use with #4 - 3/0 AWG BURNDY® Overhead Distribution Connectors Only

By Burndy
Catalog # [PATMD430LWJAW](#)

PATMD-LW IN-LINE® 6T Scissor Action, 430 Dieless Crimper Jaw for #4 - 3/0 AWG BURNDY® OH Dist Conn Only.

Features

- 430 Dieless Crimping only for specific overhead distribution connectors
- Interchangeable scissor action jaws
- Locking jaw tabs
- for PATMD-LW series

Application

Crimping and Cutting

General

Catalog Number	PATMD430LWJAW
Crimp Force Capacity	6 ton
Die Type	Dieless
Tool Type	Crimper Jaw
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	621945561922

Dimensions

Dimensions	4.21 in x 4.27 in x 1.0625 in
Height	1.0625 in
Length	4.21 in



Weight	2 lb
Width	4.27 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Utility distribution splices: #4 AWG - 3/0 AWG
-----------------	--

Logistics

Carton Quantity	1
Package Contents	430 Dieless Crimper Jaw for PATMD-LW Tool
Pallet Quantity	464

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50054521](#)
- [Specifications - PATMD430LWJAW](#)
- [Video - BURNDY PATMD-LW](#)