



# PATRIOT® IN-LINE® 6-Ton Scissor Action, GUY Cut Jaw, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Utility Bag

By Burndy  
Catalog # [PATMD60005A1](#)

PATMD-LW IN-LINE® 6T Scissor Action, GUY Cut Jaw, 5Ah Li-ion, AC, Utility Bag.



## Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

## General

|                          |  |
|--------------------------|--|
| Application              | Crimping and Cutting   |
| Application - For Use On | Interchangeable Jaws: Crimp: ACSR, Aluminum, Copper Code/Flex; Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately) |
| Battery Type             | 5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)   |
| Catalog Number           | PATMD60005A1   |
| Container Type           | Vinyl Utility Bag  |
| Crimp Force Capacity     | 6 ton  |
| Die Type                 | W Die and X Die  |
| Power Source             | 120V-AC Charger  |
| Recharge Time            | 0.75 h   |
| Tool Type                | Battery Actuated Scissor Action  |
| Trade Name               | PATRIOT® IN-LINE®  |
| Type                     | Crimper and Cutter   |
| UPC                      | 621945546646   |
| UPC 12 Digit             | 621945546646   |

## Dimensions

|            |                               |
|------------|-------------------------------|
| Dimensions | 19.25 in x 4.375 in x 2.75 in |
| Height     | 2.75 in                       |
| Length     | 19.25 in                      |
| Weight     | 5.55 lb                       |
| Width      | 4.375 in                      |

## Electrical Ratings

|                   |        |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

## Conductor Related

|                 |  |
|-----------------|--|
| Crimping Ranges | With Appropriate Jaw:<br>Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG; Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8" |
|-----------------|--|

## Logistics

|                  |  |
|------------------|--|
| Carton Quantity  | 1  |
| Package Contents | Tool, GUY Cut Jaw, (2) Batteries, Charger, Utility Bag |
| Pallet Quantity  | 30   |

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Video - BURNDY PATMD-LW](#)
- [Video - BURNDY EHS Guy Wire cutting jaw](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-PATMD60005A1-SPEC-EN | REV 6/2024