



PATRIOT® IN-LINE® 6-Ton Scissor Action, Crimper Jaw with Permanent BG & D3 Grooves (Jaw Only)

By Burndy
Catalog # [PATMD6LWJAW](#)



PATMD-LW IN-LINE® 6T Scissor Action, Crimper Jaw with Permanent BG & D3 Grooves (Jaw Only).

Features

- Crimp jaw with permanent BG/D3 grooves
- Interchangeable scissor action jaw
- Locking jaw tabs
- Uses W and X dies
- for PATMD-LW series batteries

Application

Crimping and Cutting

General

Application - For Use On	Crimping with Permanent BG/D3 Die Grooves, W & X Dies
Catalog Number	PATMD6LWJAW
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
EU RoHS Indicator	Contact Manufacturer
Tool Type	Crimper Jaw
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	621945483477
UPC 12 Digit	621945483477

Dimensions

Dimensions	5.06 in x 4.27 in x 1.0625 in
Height	1.0625 in

Length	5.06 in
Weight	2 lb
Width	4.27 in

Conductor Related

Crimping Ranges	Copper: #10 sol. - 500 kcmil, Copper Flex: #8 AWG - 350 kcmil, Aluminum: #14 sol. - 350 kcmil, ACSR: #14 sol. - 4/0 AWG
-----------------	---

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

Logistics

Minimum Pack Quantity	1
Package Contents	BG/D3 Crimper Jaw for PATMD-LW Tool

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR_PATMD-LW](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50054529](#)
- [Specifications - PATMD6LWJAW](#)
- [Video - BURNDY PATMD-LW](#)