



PATRIOT® IN-LINE® 6-Ton Scissor Action, 430 Dieless Crimp Jaw, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Utility Bag

By Burndy
Catalog # [PATMD80005A1](#)

PATMD-LW IN-LINE® 430 Dieless Crimp Jaw, 5Ah Li-ion, AC, Vinyl Utility Bag.



Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

General

Application	Crimping and Cutting
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PATMD80005A1
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
EU RoHS Indicator	Contact Manufacturer
Recharge Time	0.75 h
Sub Brand	PATRIOT IN-LINE
Tool Type	Battery Actuated Scissor Action
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	621945616486

Dimensions

Dimensions	18.1 in x 4.375 in x 2.75 in
Height	2.75 in
Length	18.1 in
Weight	5.55 lb
Width	4.375 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Utility distribution splices: #4 AWG - 3/0 AWG
-----------------	--

Logistics

Carton Quantity	1
Package Contents	Tool, 430 Dieless Crimp Jaw, (2) Batteries, Charger, Lanyard, Utility Bag
Pallet Quantity	30

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50054521](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Video - BURNDY PATMD-LW](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-PATMD80005A1-SPEC-EN | REV 6/2024