



PATRIOT® IN-LINE® 6-Ton Scissor Action, Cutter Jaw ACSR Replacement Blade Set

By Burndy
Catalog # [PATMDCUTACSRKIT](#)



PATMD-LW IN-LINE® 6T Scissor Action, Cutter Jaw ACSR Replacement Blade Set (Contains 2 Blades Only).

Features

- ACSR Replacement Blade Set
- Contains 2 Blades Only
- For use with PATMDCUTLWJAW

Application

Crimping and Cutting

General

Application - For Use On	Cutting ACSR (26/7) Cable up to 556.5 kcmil
Crimp Force Capacity	6 ton
Power Source	120V-AC Charger
Tool Type	Battery Actuated Scissor Action
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	781810570012
UPC 12 Digit	781810570012

Dimensions

Weight	0.45 lb
--------	---------

Conductor Related

Crimping Ranges	Cutting Capacity: ACSR (26/7) up to 556.5 kcmil; Aluminum (AAC) up to 636 kcmil; Copper (soft drawn) up to 350 kcmil
-----------------	----------------------------------------------------------------------------------------------------------------------

Certifications and Compliance

Standards - RoHS Compliance UI Status

Logistics

Minimum Pack Quantity	1
Package Contents	ACSR Replacement Blade Set (Contains 2 Blades only) for PATMD-LW Cutter Jaw

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-PATMDCUTACSRKIT-SPEC-EN | REV 1/2024