



PATRIOT® IN-LINE® 6-Ton Scissor Action Cutter Jaw for CU/AL (Jaw Only)

By Burndy
Catalog # [PATMDCUTCLWJAW](#)



PATMD-LW IN-LINE® 6T Scissor Action Cutter Jaw for CU/AL (Jaw Only).

Features

- Use with CU/AL cable
- Interchangeable scissor action jaw
- Locking jaw tabs
- for PATMD-LW series

Application

Crimping and Cutting

General

Application - For Use On	Cutting Aluminum and Copper Cable
Catalog Number	PATMDCUTCLWJAW
Crimp Force Capacity	6 ton
Tool Type	Cutter Jaw
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	621945528772
UPC 12 Digit	621945528772

Dimensions

Dimensions	5.52 in x 3.94 in x 1.375 in
Height	1.375 in

Length	5.52 in
Weight	2.5 lb
Width	3.94 in

Conductor Related

Crimping Ranges	Cutting Capacity: Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil
-----------------	---

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	CU/AL Cutter Jaw for PATMD-LW Tool
Pallet Quantity	464

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50054529](#)
- [Specifications - PATMDCUTCLWJAW](#)
- [Video - BURNDY PATMD-LW](#)