



PATRIOT® IN-LINE® 6-Ton Scissor Action, Cutter Jaw CU/AL Replacement Blade Set

By Burndy
Catalog # [PATMDCUTCUALKIT](#)

PATMD-LW IN-LINE® 6T Scissor Action, Cutter Jaw CU/AL Replacement Blade Set.



Features

- Unique CU/AL Wire blades for PATMDCUTCLWJAW

General

Application	Crimping and Cutting
Application - For Use On	Cutting Aluminum and Copper Cable
Catalog Number	PATMDCUTCUALKIT
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
Power Source	120V-AC Charger
Tool Type	Battery Actuated Scissor Action
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	621945491663
UPC 12 Digit	621945491663

Dimensions

Weight	0.45 lb
--------	---------

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Cutting Capacity: Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil
-----------------	---

Logistics

Minimum Pack Quantity	1
Package Contents	Cutter Jaw CU/AL Replacement Blade Set (Contains 2 Blades only) for PATMD-LW Cutter Jaw

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)



A Hubbell brand