



PATRIOT® IN-LINE® 6-Ton Scissor Action Cutter Jaw for EHS GUY (Jaw Only)

By Burndy

Catalog # [PATMDCUTGLWJAW](#)



PATMD-LW IN-LINE® 6T Scissor Action Cutter Jaw for EHS GUY (Jaw Only).

Features

- Use with EHS Guy cable
- Interchangeable scissor action jaw
- Locking jaw tabs
- for PATMD-LW series

Application

Crimping and Cutting

General

Application - For Use On	Cutting EHS Guy Wire up to 3/8" diameter
Catalog Number	PATMDCUTGLWJAW
Crimp Force Capacity	6 ton
Recharge Time	0.5 h
Tool Type	Cutter Jaw
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	621945545854
UPC 12 Digit	621945545854

Dimensions

Dimensions	5.52 in x 3.94 in x 1.375 in
Height	1.375 in
Length	5.52 in

Weight	2.5 lb
Width	3.94 in

Conductor Related

Crimping Ranges	Cutting Capacity: EHS Guy Wire up to 3/8" diameter
-----------------	----------------------------------------------------

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	EHS GUY Cutter Jaw for PATMD-LW Tool
Pallet Quantity	464

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50054529](#)
- [Specifications - PATMDCUTGLWJAW](#)
- [Video - BURNDY EHS Guy Wire cutting jaw](#)
- [Video - BURNDY PATMD-LW](#)

