

# PATRIOT® IN-LINE® 6-Ton Scissor Action Cutter Jaw for ACSR (Jaw Only)

By Burndy  
Catalog # [PATMDCUTLWJAW](#)



PATMD-LW IN-LINE® 6T Scissor Action Cutter Jaw for ACSR (Jaw Only).

## Features

- Use with ACSR cable
- Interchangeable scissor action jaw
- Locking jaw tabs
- for PATMD-LW series

## Application

Crimping and Cutting

## General

Application - For Use On	Cutting ACSR (26/7) Cable up to 556.5 kcmil
Catalog Number	PATMDCUTLWJAW
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
EU RoHS Indicator	Contact Manufacturer
Power Source	120V-AC Charger
Recharge Time	0.5 h
Sub Brand	PATRIOT® IN-LINE® CUTTER JAW
Tool Type	Cutter Jaw
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	621945483460
UPC 12 Digit	621945483460

## Dimensions

Dimensions	5.82 in x 4.58 in x 1.375 in
Height	1.375 in

Length	5.82 in
Weight	2.5 lb
Width	4.58 in

## Conductor Related

Crimping Ranges	Cutting Capacity: ACSR (26/7) up to 556.5 kcmil; Aluminum (AAC) up to 636 kcmil; Copper (soft drawn) up to 350 kcmil
-----------------	----------------------------------------------------------------------------------------------------------------------

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	ACSR Cutter Jaw for PATMD-LW Tool
Pallet Quantity	464

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR\\_PATMD-LW](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50054529](#)
- [Specifications - PATMDCUTLWJAW](#)
- [Video - BURNDY PATMD-LW](#)