



PATRIOT® IN-LINE® 6-Ton Scissor Action, Crimper Jaw with Permanent X, P, & J die grooves (Jaw Only)

By Burndy
Catalog # [PATMDXPJLWJAW](#)



PATMD-LW IN-LINE® 6T Scissor Action, Crimper Jaw with Permanent X, P, & J die grooves (Jaw Only).

Features

- Permanent X, P, & J die grooves
- Interchangeable scissor action jaw
- Locking jaw tabs
- for PATMD-LW series

Application

Crimping and Cutting

General

Application - For Use On	Crimping with Permanent X, P, & J Die Grooves
Catalog Number	PATMDXPJLWJAW
Crimp Force Capacity	6 ton
Die Type	Permanent Die Grooves
Tool Type	Crimper Jaw
Trade Name	PATRIOT® IN-LINE®
Type	Crimper and Cutter
UPC	621945558441
UPC 12 Digit	621945558441

Dimensions

Dimensions	5.52 in x 3.94 in x 1.0625 in
Height	1.0625 in

Length	5.52 in
Weight	2.5 lb
Width	3.94 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Crimping as required with Permanent X, P, & J Die Grooves
-----------------	---

Logistics

Carton Quantity	1
Package Contents	XPJ Crimper Jaw for PATMD-LW Tool
Pallet Quantity	168

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50054521](#)
- [Specifications - PATMDXPJLWJAW](#)
- [Video - BURNDY PATMD-LW](#)