



PENA131OZ., Oxide Inhibitor, 1 Ounce Container

By Burndy
Catalog # [PENA131OZ.](#)

For Use As An Anti- Seizing Thread Lubricant, For Prevention Of Oxide Buildup.



General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Tube
Pour Point	-15 °F
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
UPC	781810105894
UPC 12 Digit	7818101058944
Viscosity at 100 Fahrenheit	250 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	1 oz.
Minimum Pack Quantity	1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[SDS - PENETROX A-13 ESPANOL SDS](#)
[SDS - PENETROX A-13 SDS](#)
[SDS - PENETROX A-13 FRENCH SDS](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-PENA131OZ-SPEC-EN | REV 6/2024