



# PENA131OZ., Oxide Inhibitor, 1 Ounce Container

By Burndy  
Catalog # [PENA131OZ.](#)

For Use As An Anti- Seizing Thread Lubricant, For Prevention Of Oxide Buildup.



## General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Tube
Pour Point	-15 °F
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
UPC	781810105894
UPC 12 Digit	7818101058944
Viscosity at 100 Fahrenheit	250 °F

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Container Size	1 oz.
Minimum Pack Quantity	1

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [SDS - PENETROX A-13 SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 ESPANOL SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 FRENCH SDS \(GHS\) \(2023-02\)](#)



A proud member of the Hubbell Family.