



PENA1355GAL, Oxide Inhibitor, 55 Gallon

By Burndy
Catalog # [PENA1355GAL](#)

Oxide Inhibiting Compound, 55 Gallon, Stored in Drum,
Recommended for Al/Al, Al/Cu , Al/Conduit Threads ,
Compatible W/ Rubber or Polyethylene Insulation.



General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Drum
Pour Point	-40 °F
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
UPC	781810023624
UPC 12 Digit	7818100236244
Viscosity at 100 Fahrenheit	250 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	55 Gallon
Minimum Pack Quantity	1

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [SDS - PENETROX A-13 SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 ESPANOL SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 FRENCH SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 GERMAN SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 ITALIAN SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 PORTUGUESE SDS \(GHS\) \(2023-02\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-PENA1355GAL-SPEC-EN | REV 5/2024