



## PENA138, Oxide Inhibitor, 8 ounce

By Burndy  
Catalog # [PENA138](#)

Oxide Inhibiting Electrical Joint Compound, 8 OZ, For Al-Al, Al-Cu & Al Conduit Threads / Insulated Cable.



### Application

Aluminum to Aluminum, Aluminum to Conduit, Aluminum to Copper

### General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Squeeze Bottle
EU RoHS Indicator	Yes
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810592571
UPC 12 Digit	7818105925711
Viscosity at 100 Fahrenheit	250 °F

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	12
Container Size	8 oz
Minimum Pack Quantity	1
Pallet Quantity	1680

### Product Assets

- [3D Models - PENA138\\_MODEL-PDF](#)
- [3D Models - PENA138\\_MODEL-STEP](#)
- [3D Models - PENA138\\_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_PENA13\\_Lineart](#)
- [Sales Drawings - SC087706-01](#)
- [SDS - PENETROX A-13 ESPANOL SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 PORTUGUESE SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 GERMAN SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 ITALIAN SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 FRENCH SDS \(GHS\) \(2023-02\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-PENA138-SPEC-EN | REV 5/2024