



# PENA13QT, Oxide Inhibitor, Quart Container

By Burndy  
Catalog # [PENA13QT](#)

Oxide Inhibiting Electrical Joint Compound, 1 Quart, For Al-Al, Al-Cu & Al Conduit Threads / Insulated Cable.



## Application

For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit

## General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Tub
EU RoHS Indicator	Yes
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	A13
UPC	781810592922
UPC 12 Digit	7818105929222
Viscosity at 100 Fahrenheit	250 °F

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Container Size	1 Quart
Minimum Pack Quantity	1

## Product Assets

- [3D Models - PENA13QT\\_MODEL-STEP](#)
- [3D Models - PENA13QT\\_MODEL-PDF](#)
- [3D Models - PENA13QT\\_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_PENA13QT\\_LineArt](#)
- [Sales Drawings - 50016095](#)
- [SDS - PENETROX A-13 FRENCH SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 ESPANOL SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 GERMAN SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 ITALIAN SDS \(GHS\) \(2023-02\)](#)
- [SDS - PENETROX A-13 PORTUGUESE SDS \(GHS\) \(2023-02\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-PENA13QT-SPEC-EN | REV 5/2024