



# PENA255GAL, Oxide Inhibitor, 55 Gallon Container

By Burndy  
Catalog # [PENA255GAL](#)



Penetrox Oxide Inhibitor Reformulations.

## Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

## General

Catalog Number	PENA255GAL
Container Type	Drum
Trade Name	PENETROX™
UPC	781810105887
UPC 12 Digit	7818101058877

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Container Size	55 Gallon
Minimum Pack Quantity	1

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [SDS - PENETROX A2 ESPANOL SDS](#)
- [SDS - PENETROX A SDS](#)
- [SDS - PENETROX A FRENCH SDS](#)
- [SDS - PENETROX A2 SDS](#)
- [Specifications - PENA255GAL](#)