



## PENA4, Oxide Inhibitor, 4 ounce

By Burndy  
Catalog # [PENA4](#)

Oxide Inhibiting Electrical Joint Compound, 4 OZ, For Al-Al, Al-Cu & Al Conduit Threads.



### Application

Aluminum to Aluminum, Aluminum to Conduit, Aluminum to Copper

### General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA4
Container Type	Squeeze Bottle
EU RoHS Indicator	Yes
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810593103
UPC 12 Digit	7818105931033
Viscosity at 100 Fahrenheit	305 °F

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	12
Container Size	4 oz
Minimum Pack Quantity	1
Pallet Quantity	4032

### Product Assets

- [3D Models - PENA4\\_MODEL-PDF](#)
- [3D Models - PENA4\\_MODEL-IGES](#)
- [3D Models - PENA4\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sc087700-01](#)
- [SDS - PENETROX A ESPANOL SDS](#)
- [SDS - PENETROX A FRENCH SDS](#)
- [SDS - PENETROX A PORTUGUESE SDS](#)
- [SDS - PENETROX A SDS](#)
- [SDS - PENETROX A ESTONIAN SDS](#)
- [SDS - PENETROX A GERMAN SDS \(GHS\) \(2019-07\)](#)
- [Sell Sheets - PENETROX™ Overview](#)
- [Specifications - PENA4](#)