



PENACARTRIDGE, Oxide Inhibitor, Cartridge Container

By Burndy
Catalog # [PENACARTRIDGE](#)

Cartridge for PENETROX A.



General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENACARTRIDGE
Container Type	Cartridge
Pour Point	-15 °F
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
UPC	781810365502
UPC 12 Digit	7818103655022
Viscosity at 100 Fahrenheit	305 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	1 lb
Minimum Pack Quantity	1

Product Assets

- [3D Models - PENACARTRIDGE_MODEL-PDF](#)
- [3D Models - PENACARTRIDGE_MODEL-STEP](#)
- [3D Models - PENACARTRIDGE_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_PENAGAL_LineArt](#)
- [Sales Drawings - 50008001](#)
- [SDS - PENETROX A ESPANOL SDS](#)
- [SDS - PENETROX A FRENCH SDS](#)
- [SDS - PENETROX A PORTUGUESE SDS](#)
- [SDS - PENETROX A SDS](#)
- [SDS - PENETROX A ESTONIAN SDS](#)
- [SDS - PENETROX A GERMAN SDS \(GHS\) \(2019-07\)](#)
- [Specifications - PENACARTRIDGE](#)