



PENE4, Oxide Inhibitor, 4 Ounce Squeeze Bottle

By Burndy
Catalog # [PENE4](#)

Electrical sealing compound, Squeeze Bottle.



Application

For Copper To Copper

General

| | |
|-----------------------------------------|------------------|
| Application - For Use On | Copper to Copper |
| Container Type | Squeeze Bottle |
| EU RoHS Indicator | Yes |
| Pour Point | -40 °F |
| Sub Brand | PENETROX |
| Temperature - Dropping Point Fahrenheit | 350 °F |
| Trade Name | PENETROX™ |
| Type | E |
| UPC | 781810593141 |
| UPC 12 Digit | 7818105931411 |
| Viscosity at 100 Fahrenheit | 250 °F |

Certifications And Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|------|
| Container Size | 4 oz |
| Minimum Pack Quantity | 1 |

Product Assets

- [3D Models - PENE4_MODEL-STEP](#)
- [3D Models - PENE4_MODEL-IGES](#)
- [3D Models - PENE4_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Product Cross Section Image\(s\) - BUR_PENE8_LineArt](#)
- [Sales Drawings - sc087708-01](#)
- [SDS - PENETROX E PORTUGUESE SDS \(GHS\) \(2020-01\)](#)
- [SDS - PENETROX E GERMAN SDS \(GHS\) \(2020-01\)](#)
- [SDS - PENETROX E Polish SDS \(GHS\) \(2020-07\)](#)
- [SDS - PENETROX E FRENCH SDS \(GHS\) \(2020-07\)](#)
- [SDS - PENETROX E RUSSIAN SDS \(GHS\) \(2020-07\)](#)
- [SDS - PENETROX E ESPANOL SDS \(GHS\) \(2020-01\)](#)
- [SDS - PENETROX E SDS \(GHS\) \(2020-01\)](#)



A proud member of the Hubbell Family.