



PENE5GAL, Oxide Inhibitor, 5 Gallon Container

By Burndy
Catalog # [PENE5GAL](#)

Electrical Joint Compound, 5 Gallon Steel Pail, 28/26 Gauge-Black, For Cu/Cu Applications ,Grounding, Cu Conduit Threads.



General

Application - For Use On	Copper to Copper
Catalog Number	PENE5GAL
Container Type	Pail
Pour Point	-40 °F
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
UPC	781810023617
UPC 12 Digit	7818100236177
Viscosity at 100 Fahrenheit	250 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	5 Gallon
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_PENEQT_LineArt](#)
[Sales Drawings - 50016181](#)
[SDS - PENETROX E PORTUGUESE SDS](#)
[SDS - PENETROX E ESPANOL SDS](#)
[SDS - PENETROX E FRENCH SDS](#)
[SDS - PENETROX E RUSSIAN SDS](#)
[SDS - PENETROX E SDS](#)
[SDS - PENETROX E GERMAN SDS](#)
[SDS - PENETROX E Polish SDS](#)
[Specifications - PENE5GAL](#)



A Hubbell brand