



PENHT1LB, Oxide Inhibitor, 1 Pound Cartridge

By Burndy
Catalog # [PENHT1LB](#)

Electrical sealing compound, Packaged Finished Cartridges With Nozzle Down.

Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

General

Catalog Number	PENHT1LB
Container Type	Cartridge
Pour Point	-58 °F
Trade Name	PENETROX™
UPC	781810477656
UPC 12 Digit	7818104776566

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Container Size	1 lb
Minimum Pack Quantity	25

Product Assets

- [3D Models - PENHT1LB_MODEL-IGES](#)
- [3D Models - PENHT1LB_MODEL-PDF](#)
- [3D Models - PENHT1LB_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50008001](#)
- [SDS - PENETROX HT X-1552 A SDS](#)
- [SDS - PENETROX HT X-1552 A FRENCH SDS](#)
- [Specifications - PENHT1LB](#)

