



PENHT8, Oxide Inhibitor, 8 Ounce Container

By Burndy
Catalog # [PENHT8](#)

HiTemp Pen 8oz.



General

Container Type	Squeeze Bottle
Pour Point	-58 °F
Trade Name	PENETROX™
UPC	781810476567
UPC 12 Digit	7818104765677

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Container Size	8 oz
Minimum Pack Quantity	1

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - 10095801-01_E](#)
- [SDS - PENETROX HT X-1552 A SDS \(GHS\) \(2016-04\)](#)
- [SDS - PENETROX HT X-1552 A FRENCH SDS \(GHS\) \(2016-04\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-PENHT8-SPEC-EN | REV 5/2024