



PGHS1825X03D, Heat Shrink Male/Female Combination Quick Disconnect For 22 - 18 AWG (.25 x .03)



By Burndy
Catalog # PGHS1825X03D

Heat Shrink Male/Female Combination Quick Disconnect For 22 - 18 AWG (.25 x .03).

Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

Application

For Use on Copper Conductor

General

Catalog Number	PGHS1825X03D
Connector Type	Male/Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation Type	Heat Shrink
Material	Brass
Sub Brand	HYDENT
Type	Electrical Terminal
UPC	781810524084
UPC 12 Digit	7818105240844

Dimensions

Dimension - B Length inch	0.17 in
Dimension - Strip Length inch	5/16 in

Conductor Related

Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100

Product Assets

- [3D Models - PGHS1825X03D_MODEL-STEP](#)
- [3D Models - PGHS1825X03D_MODEL-PDF](#)
- [3D Models - PGHS1825X03D_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_PGHS_LineArt](#)
- [Sales Drawings - 50094217](#)
- [Specifications - PGHS1825X03D](#)