

PGN1425X03B, Nylon Male/Female Combination Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy
Catalog # [PGN1425X03B](#)



Nylon Male/Female Combination Quick Disconnect For 16 - 14 AWG (.25 x .03).

Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

General

Catalog Number	PGN1425X03B
Color	Blue
Connector Type	Male/Female Quick Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Physical Attribute - Tongue Type	Disconnect
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810327258
UPC 12 Digit	7818103272588

Dimensions

Dimension - B Length fraction	0.17
Dimension - B Length inch	0.17 in
Dimension - Inside Diameter inch	0.091 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.87 in

Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Conductor Related

Conductor Range	#14 AWG to #16 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094219](#)
- [Specifications - PGN1425X03B](#)