



## PGN1825X03D, Nylon Male/Female Combination Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy  
Catalog # PGN1825X03D

Nylon Male/Female Combination Quick Disconnect For 22 - 18 AWG (.25 x .03).

### Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

### General

Catalog Number	PGN1825X03D
Connector Type	Male/Female Quick Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293096
UPC 12 Digit	7818102930966

### Dimensions

Dimension - B Length fraction	0.17
Dimension - B Length inch	0.17 in
Dimension - F Width Center to Center inch	0.07 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.87 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm



### Conductor Related

Conductor Range	#18 AWG to #22 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

### Product Assets

- [3D Models - PGN1825X03D\\_MODEL-IGES](#)
- [3D Models - PGN1825X03D\\_MODEL-STEP](#)
- [3D Models - PGN1825X03D\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094219](#)
- [Specifications - PGN1825X03D](#)