



## PGP1025X03D, Vinyl Male/Female Combination Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy  
Catalog # PGP1025X03D



Vinyl Male/Female Combination Quick Disconnect For 12 - 10 AWG (.25 x .03).

### Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

### General

Catalog Number	PGP1025X03D
Connector Type	Male/Female Quick Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293089
UPC 12 Digit	7818102930899

### Dimensions

Dimension - B Length fraction	0.27
Dimension - B Length inch	0.27 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

### Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	17970

### Product Assets

[3D Models - PGP1025X03D\\_MODEL-IGES](#)  
[3D Models - PGP1025X03D\\_MODEL-PDF](#)  
[3D Models - PGP1025X03D\\_MODEL-STEP](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50094218](#)  
[Specifications - PGP1025X03D](#)