



PGP1825X03B, Vinyl Male/Female Combination Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # [PGP1825X03B](#)

Vinyl Male/Female Combination Quick Disconnect For 22 - 18 AWG (.25 x .03).

Features

- Tin-Plated piggy-back connectors are designed to allow for additional terminals to be connected
- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent assure firm grip

General

Catalog Number	PGP1825X03B
Color	Red
Connector Type	Male/Female Quick Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Physical Attribute - Tongue Type	Disconnect
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810327197
UPC 12 Digit	7818103271977

Dimensions

Dimension - B Length fraction	0.17
Dimension - B Length inch	0.17 in
Dimension - Inside Diameter inch	0.067 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.91 in



Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Conductor Related

Conductor Range	#18 AWG to #22 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094218](#)
- [Specifications - PGP1825X03B](#)