



# Hydraulic Hose, 10', 3/16" dia non-cond, Stackable couplers (male/female), Orange, Min burst pressure 40,000 psi, Nom working pressure 10,000 psi

By Burndy  
Catalog # [PT2990010](#)



Hydraulic Hose, 10' x 3/16" dia N/C, Stackable (M/F), Orange, 10K psi.

## Application

Accessory, Hose

## General

EU RoHS Indicator	Yes
Sub Brand	TOOLING ACCESSORY
Type	Hydraulic Accessories
UPC	781810625668

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Minimum Pack Quantity	1
Package Contents	Hose, Couplers

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SE088658-01\\_A](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-PT2990010-SPEC-EN | REV 5/2024