



Hydraulic Hose, 10', 1/4" dia non-cond, Stackable couplers (male/female), Orange, Min burst pressure 40,000 psi, Nom working pressure 10,000 psi

By Burndy
Catalog # [PT2990110](#)



Hydraulic Hose, 10' x 1/4" dia N/C, Stackable (M/F), Orange, 10K psi.

Application

Accessory, Hose

General

EU RoHS Indicator	Yes
Sub Brand	TOOLING ACCESSORY
Type	Hydraulic Accessories
UPC	781810008485

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity	1
Package Contents	Hose, Couplers

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE088658-01_A](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-PT2990110-SPEC-EN | REV 5/2024