



## Q10F25X03D, Uninsulated Female Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy  
Catalog # [Q10F25X03D](#)



Uninsulated Female Quick Disconnect For 12 - 10 AWG (.25 x .03).

### Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

### Application

Female Disconnect

### General

Catalog Number	Q10F25X03D
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293546
UPC 12 Digit	7818102935466

### Dimensions

Dimension - Length Overall inch	0.66 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.250 in
Dimension - Width mm	6 mm

### Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

### Product Assets

- [3D Models - Q10F25X03D\\_MODEL-PDF](#)
- [3D Models - Q10F25X03D\\_MODEL-IGES](#)
- [3D Models - Q10F25X03D\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094205](#)
- [Specifications - Q10F25X03D](#)