

Q14F18X02D, Uninsulated Female Quick Disconnect For 16 - 14 AWG (.19 x .02)



By Burndy
Catalog # [Q14F18X02D](#)

Uninsulated Female Quick Disconnect For 16 - 14 AWG (.19 x .02).

Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Application

For quickly connecting or disconnecting a terminal

General

Catalog Number	Q14F18X02D
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293331
UPC 12 Digit	7818102933311

Dimensions

Dimension - Length Overall inch	0.66 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.187 in
Dimension - Width mm	5 mm

Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
-----------------------------	---------------

Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

- [3D Models - Q14F18X02D_MODEL-IGES](#)
- [3D Models - Q14F18X02D_MODEL-STEP](#)
- [3D Models - Q14F18X02D_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_Q18F18X02D_LineArt](#)
- [Sales Drawings - 50094205](#)
- [Specifications - Q14F18X02D](#)