



Q14M18X02B, Uninsulated Male Quick Disconnect For 16 - 14 AWG (.19 x .02)

By Burndy
Catalog # [Q14M18X02B](#)



Uninsulated Male Quick Disconnect For 16 - 14 AWG (.19 x .02).

Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

General

Catalog Number	Q14M18X02B
Connector Type	Male Quick Disconnect
Feature - Barrel Style	Chamfered
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810327821
UPC 12 Digit	7818103278211

Dimensions

Dimension - B Length fraction	6/25 in
Dimension - B Length inch	0.24 in
Dimension - F Width Center to Center inch	0.08 in
Dimension - Length Overall inch	0.64 in
Dimension - Width inch	0.19 in
Dimension - Width mm	5 mm

Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094204](#)
[Specifications - Q14M18X02B](#)