



Q18M18X02B, Uninsulated Male Quick Disconnect For 22 - 18 AWG (.19 x .02)

By Burndy
Catalog # [Q18M18X02B](#)



Uninsulated Male Quick Disconnect For 22 - 18 AWG (.19 x .02).

Features

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

General

Catalog Number	Q18M18X02B
Connector Type	Male Quick Disconnect
Feature - Barrel Style	Chamfered
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810327548
UPC 12 Digit	7818103275488

Dimensions

Dimension - Length Overall inch	0.66 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.187 in
Dimension - Width mm	5 mm

Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	20 AWG - 18 AWG

Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094204](#)
- [Specifications - Q18M18X02B](#)