



Q2A284N, Two Conductor Four Hole Mounting Heavy Duty Copper Lug Connector, 3/0-4/0 AWG Str, 1/2" Stud, 1-3/4" Spacing, 2 Screws

By Burndy
Catalog # [Q2A284N](#)



Copper Terminal, 4 Hole, 3/0-4/0 AWG (Str), 1/2" Stud, 1-3/4" Stud Hole Spacing, 2 Screws.

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

General

Catalog Number	Q2A284N
Connector Type	Duel Clamp
Installation Torque	250 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type Plated	Hexagonal Bolt N
Plating Type	Unplated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810321485
UPC 12 Digit	7818103214855

Dimensions

Dimension - B Length inch	1.06 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.09 in
Dimension - F Width Center to Center inch	0.69 in
Dimension - Height fraction	1-3/8 in
Dimension - Height inch	1.31 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	114 mm
Dimension - Length Overall inch	4.31 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	2.12 in
Dimension - Stud Size inch	1/2
Dimension - Width fraction	2-1/8 in
Dimension - Width inch	2.12 in
Dimension - Width mm	54 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Size	3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	3/0 AWG-4/0 AWG
Conductor Size	3/0-4/0 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity 3

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_Q2A284N_LineArt](#)
[Sales Drawings - sd023314-01](#)
[Specifications - Q2A284N](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-Q2A284N-SPEC-EN | REV 8/2024