



QA34BUSV, Undrilled Silver Plated Heavy Duty One Hole Copper Lug Connector, 400-500 kcmil, 1 Screw

By Burndy
Catalog # QA34BUSV



QIKLUG™; Silver Plated.

General

Connector Type	Single Clamp
Installation Torque Recommended in-lb	375 LBS/in
Material	Copper
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Silver
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals

Dimensions

Dimension - D inch	1.62 in
Dimension - Height fraction	1.94 in
Dimension - Height inch	1.94 in
Dimension - Hole Size inch	0.53 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.19 in
Dimension - N inch	0.81 in
Dimension - Pad Width inch	1.38 in
Dimension - Stud Size inch	1/2

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Navy Size	400 (127) Navy;500 (127) Navy
Conductor - Copper Str Navy Size Range	400 (127) Navy-500 (127) Navy
Conductor - Copper Str Size	400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	400 kcmil-500 kcmil
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - sa008947](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-QA34BUSV-SPEC-EN | REV 1/2024