



**QB312N, Right Angled Two Hole
Mounting Heavy Duty Copper Lug
Connector, 250-350 kcmil, 1/2"
Stud, 1-3/4" Spacing, 1 Screw**

By Burndy
Catalog # [QB312N](#)

Cast Cu Alloy Terminal, 2 Pad Holes, 250 kcmil - 350 kcmil, 4.50
IN L, 1.19 IN W, 9/16-18 IN Bolt.



Features

- Side Entry terminal
- Joins a range of cable at right angles to terminal blocks
- One-wrench installation

General

Catalog Number	QB312N
Connector Type	Right Angle
Installation Torque	325 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Clamping Elements	1
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type Plated	Hexagonal Bolt N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810324660

Dimensions

Dimension - B Length fraction	1-15/79 in
Dimension - B Length inch	1.19 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.25 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	1-11/16
Dimension - Height inch	1.69 in
Dimension - Height mm	42.9 mm
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	114 mm

Dimension - Length Overall inch	4.50 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.19 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Width inch	1.19 in
Dimension - Width mm	30 mm

Conductor Related

Conductor - Copper Str Size	250;300;350
Conductor - Copper Str Size Range	250-350
Conductor Size	250-350 kcmil
Conductor Type	CU C Str-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_QB_LineArt](#)
[Sales Drawings - sc023473-01](#)
[Specifications - QB312N](#)

