

QDA26CG1, Rounded Tongue Heavy Duty Copper Lug Connector, 1/0-2/0 Str, 1/2" Stud, 1 Screw

By Burndy

Catalog # [QDA26CG1](#)



Cast Cu Alloy QIKLUG Terminal, For Cu Cable, 1 Hole, 1/0-2/0 Str Commercial, 100-125 Navy, 1/2" Stud.

Features

- Compact, high copper alloy terminal
- Joins a wide range of cable to equipment studs
- Provides low contact resistance when tripped between two contact nuts
- One-wrench installation

General

Catalog Number	QDA26CG1
Connector Type	Terminal
Material	Copper
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810430682
UPC 12 Digit	7818104306822

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size
----------------	--

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - QDA26CG1](#)