

QGFL29B1, Bartap, Cable to Flat, #6 Str-250 kcmil

By Burndy
Catalog # [QGFL29B1](#)



Bartap, 6 Str. - 250 kcmil, Cable To Flat, 1/4 IN Thickness.

Application

Substation

General

Catalog Number	QGFL29B1
Connector Type	Bus Bar Clamp and Accessories
EU RoHS Indicator	Yes
Material	Copper Alloy
Material - Hardware Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Sub Brand	BARTAP
Trade Name	BARTAP™
Type	QGFL
UPC	781810325124
UPC 12 Digit	7818103251244

Dimensions

Dimension - B Length fraction	1-2/5 in
Dimension - B Length inch	1.40 in
Dimension - Height fraction	2-5/8 in
Dimension - Height inch	2.63 in
Dimension - Width fraction	1-3/8 in
Dimension - Width inch	1.38 in
Dimension - Width mm	35 mm

Conductor Related

Conductor - Copper Str Size	#6 Str;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	#6 Str-250 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - QGFL29B1_MODEL-PDF](#)
- [3D Models - QGFL29B1_MODEL-STEP](#)
- [3D Models - QGFL29B1_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_QGFL_LineArt](#)
- [Sales Drawings - SA045357](#)
- [Specifications - QGFL29B1](#)