

Substation - Copper Bar Tap

By Burndy
Catalog # [QGFL39B1](#)

Bartap, 350 - 750 kcmil, Cable To Flat.



Application

Substation

General

Catalog Number	QGFL39B1
Connector Type	Bus Bar Clamp and Accessories
EU RoHS Indicator	Yes
Material	Copper Alloy
Material - Hardware Plated	DURIUM™ Silicon Bronze
Plating Type	N
Sub Brand	BARTAP
Trade Name	BARTAP™
Type	QGFL
UPC	781810005880
UPC 12 Digit	7818100058800

Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - Height fraction	3-1/4 in
Dimension - Height inch	3.25 in
Dimension - Width fraction	1-3/4 in
Dimension - Width inch	1.75 in
Dimension - Width mm	44 mm

Conductor Related

Conductor - Copper Str Size	350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Size Range	350 kcmil-750 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_QGFL_LineArt](#)
[Sales Drawings - SA045357](#)
[Specifications - QGFL39B1](#)