

# QN10F25X03B, Nylon Female Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy  
Catalog # [QN10F25X03B](#)



Nylon Female Quick Disconnect For 12 - 10 AWG (.25 x .03).

## Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

## General

Catalog Number	QN10F25X03B
Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
UPC	781810292921
UPC 12 Digit	7818102929211

## Dimensions

Dimension - B Length fraction	3/13 in
Dimension - B Length inch	0.23 in
Dimension - F Width Center to Center inch	0.13 in
Dimension - Length Overall inch	0.97 in

## Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards	UL310
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Pallet Quantity	99999

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - QN10F25X03B](#)