

## QN10M25X03D, Nylon Male Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy  
Catalog # [QN10M25X03D](#)



Nylon Male Quick Disconnect For 12 - 10 AWG (.25 x .03).

### Features

- Sleeved barrel
- Funnel entry barrel opening assures quick and easy wire insertion
- Mates with dimpled female socket detent ensuring firm grip

### Application

Male Disconnect

### General

Catalog Number	QN10M25X03D
Connector Type	Male Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810525043
UPC 12 Digit	7818105250433

### Dimensions

Dimension - Length Overall inch	0.95 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

### Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

### Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	600
Minimum Pack Quantity	50

### Product Assets

- [3D Models - QN10M25X03D\\_MODEL-PDF](#)
- [3D Models - QN10M25X03D\\_MODEL-STEP](#)
- [3D Models - QN10M25X03D\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_L6FQNM\\_LineArt](#)
- [Sales Drawings - 50094209](#)
- [Specifications - QN10M25X03D](#)