

QN14F11X02D, Nylon Female Quick Disconnect For 16 - 14 AWG (.11 x .02)

By Burndy
Catalog # [QN14F11X02D](#)



Nylon Female Quick Disconnect For 16 - 14 AWG (.11 x .02).

Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

Application

Female Disconnect

General

Catalog Number	QN14F11X02D
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Under Review
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810525616
UPC 12 Digit	7818105256166

Dimensions

Dimension - Length Overall inch	0.77 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.11 in
Dimension - Width mm	3 mm

Electrical Ratings

Voltage - Maximum 300 V

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards	UL310
Met	
Standards - RoHS Compliance	UI
Status	
UL Listed	No

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094210](#)
- [Specifications - QN14F11X02D](#)