



Nylon Female Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy
Catalog # [QN14FF250D](#)



Nylon Female Quick Disconnect For 16 - 14 AWG (.25 x .03).

General

Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810038345

Dimensions

Dimension - B Length fraction	19/50 in
Dimension - B Length inch	0.38 in
Dimension - D inch	0.16 in
Dimension - Length Overall inch	0.89 in
Dimension - Pad Width inch	0.23 in

Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[3D Models - QN14FF250D_MODEL-IGES](#)
[3D Models - QN14FF250D_MODEL-STEP](#)
[3D Models - QN14FF250D_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_QN14FF250D_LineArt](#)
[Sales Drawings - 30015719](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-QN14FF250D-SPEC-EN | REV 5/2024