

# QN18F25X03B, Nylon Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy  
Catalog # [QN18F25X03B](#)



## Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

## General

|                 |                         |
|-----------------|-------------------------|
| Catalog Number  | QN18F25X03B             |
| Connector Type  | Female Quick Disconnect |
| Insulation      | Y                       |
| Insulation Type | Nylon                   |
| Material        | Brass                   |
| Plated          | Y                       |
| Plating Type    | Tin                     |
| Trade Name      | FINGRIP™                |
| Type            | Disconnect Connectors   |
| UPC             | 781810292693            |
| UPC 12 Digit    | 7818102926933           |

## Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Length Overall inch | 0.87 in |
| Dimension - Strip Length inch   | 3/8 in  |
| Dimension - Width inch          | 0.25 in |
| Dimension - Width mm            | 6 mm    |

## Electrical Ratings

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 300 V |
|-------------------|-------|

## Conductor Related

|                 |  |
|-----------------|--|
| Conductor Range | #22 AWG to #16 AWG   |
| Conductor Size  | 22 - 18 AWG  |
| Conductor Type  | <ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul> |

## Certifications And Compliance

|                                |       |
|--------------------------------|-------|
| Certification - CSA Approved   | No    |
| Certification - ETL            | No    |
| Certification - UL Recognized  | No    |
| Certification - cULus          | Yes   |
| Standards - Industry Standards | UL310 |
| Met                            |       |
| Standards - RoHS Compliance    | UI    |
| Status                         |       |
| UL Listed                      | No    |

## Logistics

|                       |       |
|-----------------------|-------|
| Carton Quantity       | 1000  |
| Minimum Pack Quantity | 1000  |
| Pallet Quantity       | 99999 |

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094210](#)
- [Specifications - QN18F25X03B](#)