

QN18F25X03D, Nylon Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # [QN18F25X03D](#)



Nylon Female Quick Disconnect For 22 - 18 AWG (.25 x .03).

Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

Application

For quickly connecting or disconnecting a terminal

General

Catalog Number	QN18F25X03D
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293232
UPC 12 Digit	7818102932322

Dimensions

Dimension - Length Overall inch	0.87 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Electrical Ratings

Voltage - Maximum 300 V

Conductor Related

Conductor Range	#22 AWG to #16 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_L6FQNF_LineArt](#)
- [Sales Drawings - 50094210](#)
- [Specifications - QN18F25X03D](#)